

*Feel Different*

# CE-9

MANUAL BLOCKER



## CE-9 Specifications

Lens Size	Dia. 80 mm or less
Layout Span	horizontal: $\pm 15$ mm or over vertical: $\pm 5$ mm or over Slide center blocking
Light Source	White LED
Blocking Method	Manual blocking method
Blocking Accuracy	Position: Dia. 0.5 mm or less Axis angle: $\pm 0.5^\circ$ mm or less
Power Supply	AC 100 V $\pm 10\%$ to 240 V $\pm 10\%$ 50 / 60 Hz
Power Consumption	15 VA
Dimensions & Weight	115 (W) x 160 (D) x 214 (H) mm / 1.7 kg 4.53 (W) x 6.3 (D) x 8.43 (H) " / 3.75 lbs.
Standard Accessories	Power code (x1), Frame change holder (x1)

## Key Features

- Maintenance-free LED light improved cost efficiency
- Light control for optimum visibility
- Compact and stylish design



Eye & Health Care  
**NIDEK CO., LTD.**

### HEAD OFFICE

34-14 Maehama, Hiroishi  
Gamagori, Aichi 443-0038, Japan  
Telephone : 81-533-67-6611  
Facsimile : 81-533-67-6610  
URL : <http://www.nidek.co.jp>

### TOKYO OFFICE

(International Div.)  
3F Sumitomo Fudosan Hongo Bldg.,  
3-22-5 Hongo, Bunkyo-ku, Tokyo,  
113-0033 Japan  
Telephone : 81-3-5844-2641  
Facsimile : 81-3-5844-2642  
URL : <http://www.nidek.com>

### NIDEK INC.

47651 Westinghouse Drive  
Fremont, CA 94539, U.S.A.  
Telephone : 1-510-226-5700  
                  : 1-800-223-9044 (US only)  
Facsimile : 1-510-226-5750  
URL : <http://www.usa.nidek.com>

### NIDEK SOCIÉTÉ ANONYME

Europarc  
13, rue Auguste Perret  
94042 Créteil, France  
Telephone : 33-1-49 80 97 97  
Facsimile : 33-1-49 80 32 08  
URL : <http://www.nidek.fr>

### NIDEK TECHNOLOGIES SRL.

Via dell'Artigianato, 6 / A  
35020 Albignasego (Padova), Italy  
Telephone : 39 049 8629200 / 8626399  
Facsimile : 39 049 8626824  
URL : <http://www.nidektechnologies.it>

\*Specifications and design are subject to change without notice for improvement.



Printed on environment-friendly recycled paper.